

GRAB RAILS & BACK RESTS



MLR112_DESIGNER

90° Ambulant Grab Rail 450x450mm in Designer Black



Specification

Material	#304 Stainless Steel - 32mmØ
Finish	Designer Matte Black
Mounting	Concealed Fix - 78mmØ Mount
Also Available	MLR112: Satin Stainless Steel ANMB MLR112: Antimicrobial
Note	Suits Right Hand or Left Hand installation

* This unit is accessible compliant when installed in accordance with AS1428.1 guidelines.

*It is the responsibility of the installer to ensure that the surface/substrate that the unit is installed upon and the fixings used are suitable to withstand the weight bearing loads of the unit and if required as per AS1428 / Australian building code regulations.

*The materials and construction of this grab rail meets AS1428.1 force requirements to be able to withstand a force of 1100Nm applied at any position and in any direction without deformation.



Downloads & Resources

- [Care & Maintenance](#)
- [Installation instructions](#)
- [Revit](#)
- [Promotions](#)
- [Associated Videos](#)
- [Stainless Steel Maintenance & Cleaning](#)

The photographs and line drawings of the products presented above are representational only. Metlam Australia Pty Ltd reserves the right to, and from time to time, make changes and improvements in design and dimensions.