

GRAB RAILS & BACK RESTS

MLR121RH_SET

40° Grab Rail & Backrest Set RH

Specification

Material	#304 Satin Stainless Steel Frame & Mounts
Finish	Satin Stainless Steel Right Hand Set with MLR 119 C
Mounting	Concealed Fix
Backrest Standoff	Adjustable depth to suit installation requirements
Note	Installation instructions provided This set consists of: • MLR121RH_X • MLR119CMKII • MLR_BR_350 *** Pieces can be sold separately if required ***

* This unit is accessible compliant when installed in accordance with AS1428.1, guidelines and when installed with the appropriate cistern.

*It is the responsibility of the installer to ensure that the surface/substrate that the unit is installed upon and the fixings used are suitable to withstand the weight bearing loads of the unit and if required as per AS1428 / Australian building code regulations.

*The materials and construction of this grab rail meets AS1428.1 force requirements to be able to withstand a force of 1100Nm applied at any position and in any direction without deformation.

Downloads & Resources

- Care & Maintenance
- Installation instructions
- Auto cad
- Archi cad
- Associated Videos
- Stainless Steel Cleaning & Maintenance

The photographs and line drawings of the products presented above are representational only.
Metlam Australia Pty Ltd reserves the right to, and from time to time, make changes and improvements in design and dimensions.

